

## Bench Top Ring Mill

BTRM | Quiet and efficient pulveriser.



### The main features.

- Small and compact to fit on a work bench.
- Very low contamination of samples
- Low maintenance
- Noise level less than 80 dBA

### The process.

Used for pulverising a variety of material from 1g - 100g for subsequent analysis by instrumental methods or wet chemistry.

## Bench Top Ring Mill

BTRM | Quiet and efficient pulveriser.

### Specifications

Motor power	0.18kW, 3 phase or single phase
Maximum input particle size	Recommended 2-5mm sample, 8mm maximum.
Product size	Typically 95% - 100µm, samples can be pulverized <75µm
Width x Height x Depth	410 x 510 x 410mm
Weight	67kg
Sample size	1g - 100g
Dust extraction	NA
Options	NA
Warranty	Rocklabs Bench Top Ring Mill is sold with a 2000 operating hours or one year warranty (whichever comes first), covering all parts (excluding wear parts) and labour if used under normal laboratory conditions.

### \*Head Options

Carbon / Chrome	40
Carbon / Chrome	100
Tungsten Carbide	40
Zirconia	40

### Shipping Dimensions

Width	665mm
Height	685mm
Depth	610mm
Weight	80kg

\*For more information please contact us on the details below or visit the website for a list of international agents.

**ROCKLABS Ltd.**  
P.O Box 18-142, Glen Innes 1743,  
Auckland, New Zealand.

**P** 64 9 634 7696  
**F** 64 9 634 6896  
**E** sales@rocklabs.com

[www.rocklabs.com](http://www.rocklabs.com)